



Relief techniek met 3D Liner

v15080

3D liners zijn ideaal voor het toevoegen van een patroonstructuur aan oppervlakken die kunnen worden bewerkt met een patina-techniek. Trek lijnen direct op het oppervlak met de tekentip op de fles en laat drogen. Plus Color hobbyverf is uitstekend om over te wrijven met een foam stencil brush - een leuke en opwindende techniek.

Hoe werkt het



1 The relief paint 3D liner is applied with the drawing tip on the bottle. Choose whether you want a patterned structure to cover the surface of the product completely or partially. Here we have chosen white which appears neutral, but all the 3D liner colours will have different effect. Leave to dry for 8-10 hours.



2 Paint the wooden item with Plus Color craft paint (which has an excellent opacity).



3 Rub a foam stencil brush in light, circular movements over the 3D liner surface design before the paint dries so that you rub off some of the paint. You may slightly moisten the foam stencil brush.





4 Depending on the look you prefer, you can dab on top of the 3D design using, for example, Art Metal gold paint. Most importantly, when applying a patina, all paint application must be slightly transparent in order to achieve the best effect.